

Mitutoyo**Digital internal micrometer with data output, Measuring range: 5-30mm****Order data**

Order number	426850 5-30
GTIN	4946368696157
Item class	44A

Description**Version:**

Direct reading from digital display. Fully hardened, ground and lapped spindle. Carbide tipped jaws, ground and precision lapped. Constant measuring force due to precision ratchet. With locking screw.

Callout:

Preset to any initial value.

Zeroing in any position without clearing down the absolute value.

Data storage button allows the measured results to be stored (e.g. in inconvenient measuring positions)

Accuracy:

Up to 30 mm: 5 μ m / from 30 mm: 6 μ m.

Supplied with:

1 battery No. 081560 size 357.

Optional extras:

Data cable No. 497445, Setting rings No. 484030.

Technical description

Measuring range	5 - 30 mm
Scale divisions	0.001 mm
Article no of the battery / rechargeable battery fitted	081560 357
Number of batteries contained	1

Power supply	Battery-powered
Standard	Manufacturer's standard
Interface	Digimatic interface
Interface	USB interface
Measurement technology	digital
Packaging	sturdy box
Calibration	B4
Type of product	Internal micrometer

Services

CalibrationInternal micrometer maximum measuring range 50 mm	022360 50
--	-----------

Accessories

Receiver / USB keyboard interface Type	498965
Multi-receiver / USB keyboard interface Type	498975
Connecting cablewith data switch Type USB2	497445 USB2
Setting ringDIN 2250 C Nominal size Ø 10 mm	484030 10
Connecting cablewith data switch Type D2	497445 D2
Setting ringDIN 2250 C Nominal size Ø 20 mm	484030 20
Button cell / special battery Battery type 357	081560 357
Setting ringDIN 2250 C Nominal size Ø 30 mm	484030 30
Transmitter Type S16E	498966 S16E
Connecting cablewith data switch Type D1	497445 D1