



External micrometer with disc anvils, Measuring range: 75-100mm



Order data

Order number	423000 75-100
GTIN	4045197204035
Item class	42B

Description

Version:

With large-area, hardened disc anvils. Forged and enamelled frame.
Design with rotating spindle.

Application:

For determining the tooth widths of spur and helical gears from module 0.8.

Supplied with:

From size 25-50 including 1 setting standard.

Technical description

Micrometer barrel graduations	1/50 mm
Measuring range	75 - 100 mm
Spindle Ø	8 mm
Disc anvil Ø	20 mm
Parallelism of the measuring faces	5 µm
Spindle pitch	0.5 mm
Scale divisions	0.01 mm
Calibration	B2
Standard	DIN 863
Measurement technology	analogue

Packaging	sturdy box
Type of product	External micrometer

Services

DAkkS calibration External micrometer including setting dimension maximum measuring range 100 mm	022050 100
Calibration External micrometer including setting dimension maximum measuring range 100 mm	022040 100

Accessories

Micrometer setting standard overall length 75 mm	421100 75
--	-----------