

**Mitutoyo****Digital internal micrometer with data output, Measuring range: 25-50mm****Order data**

Order number	426850 25-50
GTIN	4946368511306
Item class	44A

**Description****Version:**

**Direct reading from digital display.** Fully hardened, ground and lapped spindle. Carbide tipped jaws, ground and precision lapped. Constant measuring force due to precision ratchet. With locking screw.

**Callout:**

Preset to any initial value.

Zeroing in any position without clearing down the absolute value.

Data storage button allows the measured results to be stored (e.g. in inconvenient measuring positions)

**Accuracy:**

Up to 30 mm: 5  $\mu$ m / from 30 mm: 6  $\mu$ m.

**Supplied with:**

1 battery No. 081560 size 357.

**Optional extras:**

Data cable No. 497445, Setting rings No. 484030.

**Technical description**

Measuring range	25 - 50 mm
Scale divisions	0.001 mm
Article no of the battery / rechargeable battery fitted	081560 357
Number of batteries contained	1

Power supply	Battery-powered
Standard	Manufacturer's standard
Interface	Digimatic interface
Interface	USB interface
Measurement technology	digital
Packaging	sturdy box
Calibration	B4
Type of product	Internal micrometer

### Services

CalibrationInternal micrometer maximum measuring range 50 mm	022360 50
--	-----------

### Accessories

Connecting cablewith data switch Type USB2	497445 USB2
Setting ringDIN 2250 C Nominal size Ø 40 mm	484030 40
Receiver / USB keyboard interface Type	498965
Connecting cablewith data switch Type D1	497445 D1
Setting ringDIN 2250 C Nominal size Ø 50 mm	484030 50
Setting ringDIN 2250 C Nominal size Ø 30 mm	484030 30
Transmitter Type S16E	498966 S16E
Multi-receiver / USB keyboard interface Type	498975
Button cell / special battery Battery type 357	081560 357
Connecting cablewith data switch Type D2	497445 D2