

**Mitutoyo****Digital micrometer head with data output, Measuring range (travel): 0-50mm****Order data**

Order number	426510 0-50
GTIN	4946368610276
Item class	44A

**Description****Version:**

**Direct reading from clear digital display. Reliable and error-free measurements - without a vernier.** Hardened and ground measuring spindle, locking by clamping screw, ratchet.

**Application:**

For installation in machines, inspection fixtures, measuring instruments etc. as an adjustable micrometer stop.

**Supplied with:**

1 battery No. 081560 size 357.

**Optional extras:**

Data cable No. 497100.

**Technical description**

Length of mounting shank	14 mm
Spindle Ø	11 mm
Overall length	172 mm
Measuring range (travel)	0 - 50 mm
Mounting shank Ø	18 mm
Barrel Ø	49 mm
Scale divisions	0.001 mm
Error limit	0.003 mm

Article no of the battery / rechargeable battery fitted	081560 357
Number of batteries contained	1
Power supply	Battery-powered
Standard	Manufacturer's standard
Interface	Digimatic interface
Interface	USB interface
Measurement technology	digital
Calibration	B3
Type of product	Micrometer head

### Services

CalibrationMicrometer head maximum measuring range 100 mm	022280 100
DAkkS calibrationMicrometer head maximum measuring range 50 mm	022290 50

### Accessories

Connecting cable Type D1	497080 D1
Transmitter Type S1	498966 S1
Connecting cablewith data switch Type D1	497100 D1
Multi-receiver / USB keyboard interface Type	498975
Connecting cablewith data switch Type D2	497100 D2
Connecting cablewith data switch Type USB2	497100 USB2
Connecting cable Type D2	497080 D2
Receiver / USB keyboard interface Type	498965
Connecting cable Type USB2	497080 USB2