

**Mitutoyo**
**Micrometer head, Measuring range (travel): 0-6,5mm**


## Order data

Order number	426200 0-6,5
GTIN	4946368020815
Item class	44A

## Description

### Version:

Fully hardened spindle and glare-free satin chrome-plated barrel. **Rotating spindle** without carbide contact face, without ratchet, **extra short version, spherical contact face.**

### Application:

For installation in machines, inspection fixtures, measuring instruments etc. as an adjustable comparator stand stop.

### Note:

Special sizes on request.

## Technical description

Radius contact face	3 mm
Barrel Ø	9 mm
Measuring range (travel)	0 - 6.5 mm
Spindle Ø	3.5 mm
Length of mounting shank	6 mm
Mounting shank Ø	6 mm
Overall length	37 mm
Scale divisions	0.01 mm
Error limit	0.002 mm
Standard	Manufacturer's standard

Micrometer barrel graduations	1/50 mm
Measurement technology	analogue
Calibration	B3
Type of product	Micrometer head

### Services

CalibrationMicrometer head maximum measuring range 25 mm	022280 25
DAkkS calibrationMicrometer head maximum measuring range 50 mm	022290 50