

Mitutoyo**Internal micrometer set, Measuring range: 50-150mm****Order data**

| | |
|--------------|---------------|
| Order number | 427500 50-150 |
| GTIN | 4946368438320 |
| Item class | 44A |

Description**Version:**

One standard micrometer head 50 – 63 mm and various extensions. **One or more extensions are screwed into the standard micrometer head, depending on the desired measuring range.** Extensions consist of cylindrical gauge blocks.

Callout:

Protective cap for thread

Extension 13 mm

Extension 25 mm

Standard micrometer head 50 - 63 mm

Accuracy:

$(3 + \text{number of extensions} + L / 50) \mu\text{m}$.

Supplied with:

Standard micrometer head and extensions.

Technical description

| | |
|----------------------|-------------|
| Number of extensions | 3 |
| Barrel \varnothing | 15 mm |
| Measuring range | 50 - 150 mm |
| Pipe \varnothing | 12.5 mm |

| | |
|-------------------------------|-----------------------------|
| Scale divisions | 0.01 mm |
| Standard | Manufacturer's standard |
| Micrometer barrel graduations | 1/50 mm |
| Measurement technology | analogue |
| Packaging | sturdy box |
| Calibration | S4 |
| Type of product | 2-point internal micrometer |

Services

| | |
|--|---------------|
| CalibrationInternal micrometer set Measuring range 50-150 mm | 020480 50-150 |
| DAkkS calibrationInternal micrometer set Measuring range 50-150 mm | 020490 50-150 |