



Internal micrometer, Measuring range: 25-50mm



Order data

Order number	426800 25-50
GTIN	4045197204134
Item class	42B

Description

Version:

Fully hardened, ground and lapped spindle. Offset and rounded jaw ends with carbide tips. Constant measuring force due to precision ratchet. Barrel with clearly engraved, black graduations. Satin chrome-plated micrometer. With adjusting screw and locking screw.

Supplied with:

Supplied with setting ring for adjustment.

Technical description

Barrel Ø	18 mm
Measuring range	25 - 50 mm
Scale divisions	0.01 mm
Error limit	12 µm
Standard	Manufacturer's standard
Micrometer barrel graduations	1/50 mm
Measurement technology	analogue
Packaging	sturdy box
Calibration	B4
Calibration	L7
Type of product	Internal micrometer

Services

CalibrationInternal micrometer maximum measuring range 50 mm	022360 50
DAkkS calibrationSetting ring maximum Ø 200 mm	028470 200
CalibrationSetting ring maximum Ø 50 mm	028400 50

Accessories

Setting ringDIN 2250 C Nominal size Ø 30 mm	484030 30
Setting ringDIN 2250 C Nominal size Ø 50 mm	484030 50
Setting ringDIN 2250 C Nominal size Ø 40 mm	484030 40