

Mitutoyo
Internal micrometer set, Measuring range: 50-300mm

Order data

Order number	427500 50-300
GTIN	4946368438337
Item class	44A

Description
Version:

One standard micrometer head 50 – 63 mm and various extensions. **One or more extensions are screwed into the standard micrometer head, depending on the desired measuring range.** Extensions consist of cylindrical gauge blocks.

Callout:

Protective cap for thread
 Extension 13 mm
 Extension 25 mm
 Standard micrometer head 50 - 63 mm

Accuracy:

$(3 + \text{number of extensions} + L / 50) \mu\text{m}$.

Supplied with:

Standard micrometer head and extensions.

Technical description

Number of extensions	5
Pipe Ø	12.5 mm
Measuring range	50 - 300 mm
Barrel Ø	15 mm

Scale divisions	0.01 mm
Standard	Manufacturer's standard
Micrometer barrel graduations	1/50 mm
Measurement technology	analogue
Packaging	sturdy box
Calibration	S4
Type of product	2-point internal micrometer

Services

CalibrationInternal micrometer set Measuring range 50-300 mm	020480 50-300
DAkkS calibrationInternal micrometer set Measuring range 50-300 mm	020490 50-300