

**Mitutoyo**
**Micrometer head, Measuring range (travel): 0-25mm**

**Order data**

Order number	426200 0-25
GTIN	4946368021898
Item class	44A

**Description**
**Version:**

Fully hardened spindle and glare-free satin chrome-plated barrel. **Rotating spindle**, with carbide tipped contact face and ratchet.

**Application:**

For installation in machines, inspection fixtures, measuring instruments etc. as an adjustable comparator stand stop.

**Note:**

Special sizes on request.

**Technical description**

Barrel Ø	18 mm
Length of mounting shank	15 mm
Mounting shank Ø	10 mm
Overall length	109 mm
Spindle Ø	6.35 mm
Measuring range (travel)	0 - 25 mm
Scale divisions	0.01 mm
Error limit	0.002 mm
Standard	Manufacturer's standard
Micrometer barrel graduations	1/50 mm
Measurement technology	analogue

Calibration	B3
Type of product	Micrometer head

**Services**

CalibrationMicrometer head maximum measuring range 25 mm	022280 25
DAkkS calibrationMicrometer head maximum measuring range 50 mm	022290 50