



Internal micrometer, Measuring range: 50-75mm



Order data

Order number	426800 50-75
GTIN	4045197204141
Item class	42B

Description

Version:

Fully hardened, ground and lapped spindle. Offset and rounded jaw ends with carbide tips. Constant measuring force due to precision ratchet. Barrel with clearly engraved, black graduations. Satin chrome-plated micrometer. With adjusting screw and locking screw.

Supplied with:

Supplied with setting ring for adjustment.

Technical description

Measuring range	50 - 75 mm
Barrel Ø	18 mm
Scale divisions	0.01 mm
Error limit	14 µm
Standard	Manufacturer's standard
Micrometer barrel graduations	1/50 mm
Measurement technology	analogue
Packaging	sturdy box
Calibration	B4
Calibration	L7
Type of product	Internal micrometer

Services

CalibrationSetting ring maximum \varnothing 100 mm	028400 100
DAkkS calibrationSetting ring maximum \varnothing 200 mm	028470 200
CalibrationInternal micrometer maximum measuring range 75 mm	022360 75

Accessories

Setting ringDIN 2250 C Nominal size \varnothing 70 mm	484030 70
Setting ringDIN 2250 C Nominal size \varnothing 60 mm	484030 60
Setting ringDIN 2250 C Nominal size \varnothing 75 mm	484030 75