

Mitutoyo**Internal micrometer set, Measuring range: 50-1000mm****Order data**

Order number	427500 50-1000
GTIN	4946368438351
Item class	44A

Description**Version:**

One standard micrometer head 50 – 63 mm and various extensions. **One or more extensions are screwed into the standard micrometer head, depending on the desired measuring range.** Extensions consist of cylindrical gauge blocks.

Callout:

Protective cap for thread

Extension 13 mm

Extension 25 mm

Standard micrometer head 50 - 63 mm

Accuracy:

$(3 + \text{number of extensions} + L / 50) \mu\text{m}$.

Supplied with:

Standard micrometer head and extensions.

Technical description

Barrel \emptyset	15 mm
Number of extensions	8
Pipe \emptyset	12.5 mm
Measuring range	50 - 1000 mm

Scale divisions	0.01 mm
Standard	Manufacturer's standard
Micrometer barrel graduations	1/50 mm
Measurement technology	analogue
Packaging	sturdy box
Calibration	S4
Type of product	2-point internal micrometer

Services

CalibrationInternal micrometer set Measuring range 50-1000 mm	020480 50-1000
DAkkS calibrationInternal micrometer set Measuring range 50-1000 mm	020490 50-1000