

 Mahr**Micrometer with dial comparator, Measuring range: 50-100mm****Order data**

Order number	424800 50-100
GTIN	2050001036650
Item class	43A

Description**Version:**

Measuring spindle of stainless steel, hardened and ground. Carbide-tipped measuring faces. Controls and reading parts satin chrome-plated. With hand temperature protection. Constant measuring force. Moveable stop anvil, retractable. Particularly suitable for series manufactured parts.

Accuracy:

Dial comparator DIN 863 – micrometer 2 µm.

Supplied with:

Dial comparator Millimes No. 434674 size 50/1.

Technical description

Measuring range	50 - 100 mm
Barrel Ø	18 mm
Graduation of the precision dial comparator	0.001 mm
Measuring range dial comparator	±0.05 mm
Spindle Ø	7.5 mm
Graduation of the micrometer	0.01 mm

Standard	DIN 863
Micrometer barrel graduations	1/50 mm
Measurement technology	analogue
Packaging	sturdy box
Calibration	B14
Type of product	Micrometer with dial comparator

Services

DAkkS calibrationMicrometer with dial comparator maximum measuring range 100 mm	022410 100
CalibrationMicrometer with dial comparator maximum measuring range 100 mm	022400 100

Accessories

Precision dial comparator \pm measuring range / reading 50/1 μm	434674 50/1
--	-------------