

Mitutoyo**Depth micrometer, Measuring range: 0-150mm****Order data**

Order number	425200 0-150
GTIN	4946368016399
Item class	44A

Description**Version:**

Various measuring depths can be achieved by exchanging the measuring pins with 25 mm increments. Measuring spindle fully hardened and ground. Base of hardened tool steel with lapped measuring anvil. Micrometer satin chrome-plated. Barrel with clearly engraved black scale and numerals. Constant measuring force due to integral ratchet.

Supplied with:

Measuring pins.

Technical description

Measuring needle Ø	4 mm
Bridge length	100 mm
Number of gauging pins	6
Barrel Ø	18 mm
Measuring range	0 - 150 mm
Scale divisions	0.01 mm

Standard	DIN 863
Micrometer barrel graduations	1/50 mm
Measurement technology	analogue
Packaging	sturdy box
Calibration	S15
Type of product	Depth micrometer

Services

CalibrationDepth micrometer set Measuring range 0-150 mm	020780 0-150
--	--------------