



## Micrometer head, Measuring range (travel): 0-13mm



### Order data

Order number	426250 0-13
GTIN	4045197204080
Item class	42B

### Description

#### Version:

Fully hardened spindle and glare-free satin chrome-plated barrel. **Rotating spindle**, without carbide contact face, without ratchet, **short version**.

#### Application:

For installation in machines, inspection fixtures, measuring instruments etc. as an adjustable comparator stand stop.

### Technical description

Overall length	58.5 mm
Measuring range (travel)	0 - 13 mm
Spindle Ø	5 mm
Length of mounting shank	9.5 mm
Barrel Ø	13 mm
Mounting shank Ø	9.5 mm
Scale divisions	0.01 mm
Error limit	0.002 mm
Standard	Manufacturer's standard
Micrometer barrel graduations	1/50 mm
Measurement technology	analogue

Calibration	B3
Type of product	Micrometer head

**Services**

CalibrationMicrometer head maximum measuring range 25 mm	022280 25
DAkkS calibrationMicrometer head maximum measuring range 50 mm	022290 50