

Mitutoyo**Internal micrometer, Measuring range: 25-50mm****Order data**

Order number	426805 25-50
GTIN	4946368019888
Item class	44A

Description**Version:**

Fully hardened, ground and lapped spindle. Offset and rounded jaw ends with carbide tips. Constant measuring force due to precision ratchet. Barrel with clearly engraved, black graduations. Satin chrome-plated micrometer. With adjusting screw and locking screw.

Optional extras:

Setting ring No. 484030.

Technical description

Measuring range	25 - 50 mm
Barrel Ø	18 mm
Scale divisions	0.01 mm
Error limit	6 µm
Standard	Manufacturer's standard
Micrometer barrel graduations	1/50 mm
Measurement technology	analogue
Packaging	sturdy box
Calibration	B4
Type of product	Internal micrometer

Services

CalibrationInternal micrometer maximum measuring range 50 mm

022360 50

Accessories

Setting ringDIN 2250 C Nominal size Ø 32 mm

484030 32

Setting ringDIN 2250 C Nominal size Ø 46 mm

484030 46

Setting ringDIN 2250 C Nominal size Ø 30 mm

484030 30

Setting ringDIN 2250 C Nominal size Ø 38 mm

484030 38

Setting ringDIN 2250 C Nominal size Ø 44 mm

484030 44

Setting ringDIN 2250 C Nominal size Ø 42 mm

484030 42

Setting ringDIN 2250 C Nominal size Ø 26 mm

484030 26

Setting ringDIN 2250 C Nominal size Ø 35 mm

484030 35

Setting ringDIN 2250 C Nominal size Ø 40 mm

484030 40

Setting ringDIN 2250 C Nominal size Ø 36 mm

484030 36

Setting ringDIN 2250 C Nominal size Ø 45 mm

484030 45

Setting ringDIN 2250 C Nominal size Ø 34 mm

484030 34

Setting ringDIN 2250 C Nominal size Ø 28 mm

484030 28

Setting ringDIN 2250 C Nominal size Ø 25 mm

484030 25

Setting ringDIN 2250 C Nominal size Ø 50 mm

484030 50