

Garant
Parallel clamping jaw, Jaw width: 120mm

Order data

Order number	360115 120
GTIN	4045197555427
Item class	310

Description
Note:

Torque and clamping force are standard values and are only indicative reference points (material-dependent).

Technical description

Jaw width	120 mm
Clamping force	10 kN
Clamping force	20 kN
Clamping force	30 kN
Clamping force	40 kN
Torque	10 Nm
Torque	20 Nm
Torque	30 Nm
Torque	40 Nm
max. stroke	4 mm
T-bolt AF	8 mm

Shank screw AF ₁	4 mm
Type of product	Vice jaws