

**Mitutoyo****Depth micrometer, Measuring range: 0-300mm****Order data**

Order number	425200 0-300
GTIN	4946368016771
Item class	44A

**Description****Version:**

**Various measuring depths can be achieved by exchanging the measuring pins with 25 mm increments.** Measuring spindle fully hardened and ground. Base of hardened tool steel with lapped measuring anvil. Micrometer satin chrome-plated. Barrel with clearly engraved black scale and numerals. Constant measuring force due to integral ratchet.

**Supplied with:**

Measuring pins.

**Technical description**

Measuring range	0 - 300 mm
Barrel Ø	18 mm
Bridge length	100 mm
Measuring needle Ø	4 mm
Number of gauging pins	12
Scale divisions	0.01 mm

Standard	DIN 863
Micrometer barrel graduations	1/50 mm
Measurement technology	analogue
Packaging	sturdy box
Calibration	S15
Type of product	Depth micrometer

### Services

CalibrationDepth micrometer set Measuring range 0-300 mm	020780 0-300
--	--------------