



Basic assortment of clamping elements, T-slot nominal size / thread: 14/ M12mm



Order data

Order number	375410 14/M12
GTIN	4020772083892
Item class	35A

Description

Version:

- All parts made of quenched and tempered steel.
- T-slot bolts quenched and tempered, rolled thread.

Application:

Ideal for **toolmaking, manufacturing,** and **training jigs.**

Content:

Clamps: 2 pcs./ 14×100 mm; 2 pcs./ 14×160 mm

Clamp blocks: 4 pcs. / size 2; 4 pcs. size 3

T-bolts: 2 pcs./ M12×14×50 mm; 4 pcs./ M12×14×80 mm; 4 pcs./ M12×14×125 mm

Studs: 2 pcs. size M12×100

tall nuts: 6 pcs. size M12

Washers: 6 pcs. size M12

Extension nuts: 2 pcs. size M12

Technical description

T-slot nominal size	14 mm
Thread	M12

Type	6532
Type of product	Spare part clamp