



Vertical toggle clamp with horizontal base, Type: 6



Order data

Order number	376500 6
GTIN	4020772007799
Item class	35A

Description

Version:

With horizontal base for fixing to base plates etc.

- **Compact design due to new handle.**
- **Ergonomic 2-component handle, very comfortable to use due to enlarged hand rest.**
- **Captive contact screw.**
- **Finger protection thanks to safety clamping mechanism no trap points.**

Application:

For quick clamping and releasing of parts in series production or for installation as part of special clamping jigs. Suitable for clamping during drilling, reaming, grinding, bending, welding, fitting etc.

Technical description

Clamping force P2	5500 N
Bore \varnothing d	13 mm
Hole spacing e	50.5 mm
Clamping force P1	3400 N

Contact screw	M12×110 mm
overall height	333 mm
overall length	231 mm
Hole spacing f	67.5-72.5 mm
Type	6800J
Clamping height H	81 mm
Type of product	Vertical toggle clamps