

**T-bolt set, T-slot nominal size / thread: 10/M10mm****Order data**

Order number	375400 10/M10
GTIN	4020772082987
Item class	35A

**Description****Version:**

All parts quenched and tempered. Strength class 8.8 or 10.  
Presented in a sturdy wooden box with hinged lid.

**Supplied with:**

T-bolts No. 375300 DIN 787: 4 pcs./63 mm; 4 pcs./100 mm; 2 pcs./40 mm

Studs No. 375380 DIN 6379: 4 pcs./ 50 mm; 4 pcs./80 mm; 4 pcs./ 200 mm

tall nuts No. 375385 DIN 6330 B; 4 pcs.

Extension nuts No. 375395: 4 pcs.

Plain washers No. 375340 DIN 6340: 4 pcs.

Spherical seat washers and collared washers No. 375350; 375360 DIN 6319 C + G: 4 pcs.

**Technical description**

Wooden box height	32 mm
T-slot nominal size	10 mm
Wooden box width	188 mm
Thread	M10
Wooden box length	254 mm

Type	6520
Type of product	Clamping screw