

Garant**Pair of soft top jaws, for type: 80****Order data**

Order number	360146 80
GTIN	4045197642721
Item class	310

Description**Material:**

Tool steel with brief exposure nitriding.

Supplied with:

Fastening screw.

Jaw width b: 80 mm

Clamping range B - A: 130 - 153 mm

Carriage height C: 49.95 mm

D: 20 mm

Technical description

Carriage height C	49.95 mm
D	20 mm
Jaw width b	80 mm
Clamping range B - A	130 - 153 mm
Type of product	Vice - jaw