



## Vertical toggle clamp with horizontal base, Type: 0



### Order data

Order number	376500 0
GTIN	4020772007737
Item class	35A

### Description

#### Version:

With horizontal base for fixing to base plates etc.

- **Compact design due to new handle.**
- **Ergonomic 2-component handle, very comfortable to use due to enlarged hand rest.**
- **Captive contact screw.**
- **Finger protection thanks to safety clamping mechanism no trap points.**

#### Application:

**For quick clamping and releasing of parts in series production** or for installation as part of special clamping jigs. Suitable for clamping during drilling, reaming, grinding, bending, welding, fitting etc.

### Technical description

Clamping force P2	700 N
Bore Ø d	4.5 mm
Contact screw	M4×25 mm
overall length	49 mm

Hole spacing e	8.5-13.5 mm
overall height	81 mm
Hole spacing f	23 mm
Clamping force P1	500 N
Type	6800J
Clamping height H	18 mm
Type of product	Vertical toggle clamps