



Vertical toggle clamp with horizontal base, Type: 1



Order data

Order number	376500 1
GTIN	4020772007744
Item class	35A

Description

Version:

With horizontal base for fixing to base plates etc.

- **Compact design due to new handle.**
- **Ergonomic 2-component handle, very comfortable to use due to enlarged hand rest.**
- **Captive contact screw.**
- **Finger protection thanks to safety clamping mechanism no trap points.**

Application:

For quick clamping and releasing of parts in series production or for installation as part of special clamping jigs. Suitable for clamping during drilling, reaming, grinding, bending, welding, fitting etc.

Technical description

Clamping force P1	600 N
overall height	98 mm
Contact screw	M5×30 mm
Bore Ø d	4.5 mm

Hole spacing e	16 mm
Hole spacing f	22.5-26 mm
Clamping force P2	1100 N
overall length	61 mm
Type	6800J
Clamping height H	19 mm
Type of product	Vertical toggle clamps