

Garant**Pair of soft top jaws, for type: 120****Order data**

Order number	360146 120
GTIN	4045197680884
Item class	310

Description**Material:**

Tool steel with brief exposure nitriding.

Supplied with:

Fastening screw.

Jaw width b: 120 mm

Clamping range B - A: 155 - 183 mm

Carriage height C: 50 mm

D: 25 mm

Technical description

Carriage height C	50 mm
D	25 mm
Jaw width b	120 mm
Clamping range B - A	155 - 183 mm
Type of product	Vice - jaw