



Vertical toggle clamp with horizontal base, Type: 2



Order data

| | |
|--------------|---------------|
| Order number | 376500 2 |
| GTIN | 4020772007751 |
| Item class | 35A |

Description

Version:

With horizontal base for fixing to base plates etc.

- **Compact design due to new handle.**
- **Ergonomic 2-component handle, very comfortable to use due to enlarged hand rest.**
- **Captive contact screw.**
- **Finger protection thanks to safety clamping mechanism no trap points.**

Application:

For quick clamping and releasing of parts in series production or for installation as part of special clamping jigs. Suitable for clamping during drilling, reaming, grinding, bending, welding, fitting etc.

Technical description

| | |
|-------------------|----------|
| overall height | 139.5 mm |
| Clamping force P1 | 800 N |
| overall length | 78 mm |
| Hole spacing f | 23-31 mm |

| | |
|-------------------|------------------------|
| Hole spacing e | 20 mm |
| Bore Ø d | 5.5 mm |
| Contact screw | M6×35 mm |
| Clamping force P2 | 1200 N |
| Type | 6800J |
| Clamping height H | 23 mm |
| Type of product | Vertical toggle clamps |