

**T-bolt set, T-slot nominal size / thread: 18/M16mm****Order data**

Order number	375400 18/M16
GTIN	4020772083038
Item class	35A

Description**Version:**

All parts quenched and tempered. Strength class 8.8 or 10.
Presented in a sturdy wooden box with hinged lid.

Supplied with:

T-bolts No. 375300 DIN 787: 4 pcs./100 mm; 2 pcs./63 mm

Studs No. 375380 DIN 6379: 4 pcs./80 mm; 4 pcs./125 mm; 4 pcs./160 mm

T-nuts No. 375315 DIN 508: 4 pcs.

tall nuts No. 375385 DIN 6330 B: 4 pcs.

Extension nuts No. 375395: 4 pcs.

Plain washers No. 375340 DIN 6340: 4 pcs.

Spherical seat washers and collared washers No. 375350; 375360 DIN 6319 C + G: 4 pcs.

Technical description

Wooden box width	294 mm
Wooden box length	339 mm
Thread	M16
Wooden box height	48 mm

T-slot nominal size	18 mm
Type	6520
Type of product	Clamping screw