



Sliding bevel, Length of rail: 330mm



Order data

Order number	456900 330
GTIN	2050001746764
Item class	46R

Description

Version:

Innovative and versatile sliding bevel. Sturdy metal design, 330 mm spring steel blade with laser-engraved mm scale. Adjustment mechanism for 9 angular positions (30°, 45°, 60°, 75°, 90°, 105°, 120°, 145°, 160°) or stepless adjustment with a wing nut clamp.

Application:

Marking gauge, protractor, sliding square, try square, mitre square, length measurement.

Technical description

Manufacturer's designation	MW 330
Angular misalignment	±0.05 mm
Length of rail	330 mm
Angular locking	stepless adjustment with a wing nut clamp or through angular positions
adjustable angular positions	30 degrees
adjustable angular positions	45 degrees
adjustable angular positions	60 degrees
adjustable angular positions	75 degrees

adjustable angular positions	90 degrees
adjustable angular positions	105 degrees
adjustable angular positions	120 degrees
adjustable angular positions	145 degrees
Type of product	Sliding bevel