



## Assortment of clamping elements, T-slot nominal size / thread: 12/M12mm



### Order data

Order number	375405 12/M12
GTIN	4020772083595
Item class	35A

### Description

#### Version:

Consisting of various clamping elements, which are required for quick clamping of tools, jigs or components to T-slot tables. All parts are made of quenched and tempered steel and can be reordered individually.

#### Supplied with:

Combination spanner, anti-seize compound, wooden case

#### Supplied with:

T-bolts No. 375300 DIN 787: 4 pcs./ 80 mm;

4 pcs./ 125 mm;

2 pcs./ 50 mm

Studs No. 375380 DIN 6379: 4 pcs./ 100 mm

Step clamp No. 372000 DIN 6314 Z: 4 pcs./ 14x100

tall nuts No. 375385 DIN 6330 B: 6 pcs.

Extension nuts No. 375395: 4 pcs.

Universal serrated clamp support block No. 372200: 4 pcs./ size 2;

4 pcs./ size 3

Collared washer form G No. 375360 DIN 6319 G: 6 pcs.

Low height clamping jaws No. 375110: 4 pcs./ size 12

Spring clamp holder No. 370850: 4 pcs./ size 12

T-slot brush No. 375512

### Technical description

T-slot nominal size	12 mm
Clamping height quadruple set up	2 - 160 mm
Wooden box height	50 mm
Wooden box width	330 mm
Clamping height double set up	2 - 270 mm
Thread	M12
Wooden box length	460 mm
Type	6530
Type of product	Spare part clamp