



XT internal micrometer set, Measuring range: 6-10mm



Order data

Order number	428550 6-10
GTIN	5051102212100
Item class	46B

Description

Version:

3-Point **XT inside micrometers**. Measuring spindle hardened and ground. Micrometer barrel with black scale, all reading parts satin chrome-plated. Ratchet for consistent measuring force. All gauges supplied with serial number and test certificate. "Micro" - version with better resolution of 2 µm.

Application:

Blind holes and through holes, centring edges.

Supplied with:

Internal micrometers No. 428500 and setting rings with UKAS test certificate.

Optional extras:

Setting rings No. 484030, extension No. 428510.

Spare part:

Micrometer heads No. 428605.

Technical description

Setting ring Ø	8 mm
Number of setting rings	1
Measuring range	6 - 10 mm

Number of micrometers	2
Standard	DIN 863
Micrometer barrel graduations	1/50 mm
Measurement technology	analogue
Packaging	sturdy box
Calibration	S6
Type of product	3-point internal micrometer

Services

Calibration Internal micrometer set Measuring range 6-10 mm	020550 6-10
---	-------------

Accessories

XT internal micrometer Measuring range 8-10 mm	428500 8-10
Setting ring DIN 2250 C Nominal size Ø 7 mm	484030 7
Setting ring DIN 2250 C Nominal size Ø 9 mm	484030 9
Replacement XT measuring head Measuring range 8-10 mm	428605 8-10
Extension for internal micrometers Type 1/63	428510 1/63
Replacement XT measuring head Measuring range 6-8 mm	428605 6-8
XT internal micrometer Measuring range 6-8 mm	428500 6-8
Measuring jaws set 3 pieces Measuring range 6-8 mm	428745 6-8
Return spring set 3 pieces Measuring range 6-8 mm	428746 6-8
Measuring jaws set 3 pieces Measuring range 8-10 mm	428745 8-10
Return spring set 3 pieces Measuring range 8-10 mm	428746 8-10