



Internal micrometer, Measuring range: 100-125mm



Order data

Order number	427800 100-125
GTIN	2050001053640
Item class	43A

Description

Version:

Lightweight, kink-proof tubular construction. Measuring spindle through hardened and ground. **Measuring faces hardened and spherical lapped.** Control elements and reading parts satin chrome-plated. From measuring range 100 - 125 mm with thermal insulation and locking lever.

Supplied with:

Micrometer in a sleeve.

Technical description

Barrel Ø	20 mm
Measuring range	100 - 125 mm
Spindle Ø	8 mm
Scale divisions	0.01 mm
Error limit	6 µm
Standard	DIN 863
Micrometer barrel graduations	1/50 mm
Measurement technology	analogue
Calibration	B10
Type of product	2-point internal micrometer

Services

CalibrationInternal micrometer maximum measuring range 200 mm	022440 200
DAkkS calibrationInternal micrometer maximum measuring range 200 mm	022450 200