


SNMG 120408, Grade: PV720

Order data

Order number	251254 PV720
GTIN	4960664724710
Item class	25E

Technical description

Feed f	0.15 - 0.6 mm/rev.
Grade	PV720
Main application	P
Cutting conditions	continuous
Cutting depth a_p	1 - 4 mm
Chip breaker	PG
Cutting speed v_c main application	110 - 490 m/min
Corner radius	0.8 mm
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Tool material	Cermet
ISO code indexable insert	SNMG 120408
Number of changes/inserts	8

Type of product

Indexable insert for turning