

Garant**2-point quick measuring device DM1, maximum measuring range: 75mm****Order data**

Order number	428030 75
GTIN	4045197412072
Item class	41B

Description**Version:**

Solid construction for use directly on turning / milling centres. For checking internal and external diameters, concentricity, grooves, and wall thicknesses, with a **repeatability of 2 µm**.

Can be used with any dial indicator or precision dial indicator with shank \varnothing 8 h6 mm and maximum body \varnothing 62 mm (supplied without dial indicator).

Advantage:

Short measuring and set-up times, robust and easy to maintain.

Supplied with:

Measuring device fully assembled;

2 pairs of TiN-coated disc anvils (1× \varnothing 8 mm / 1× \varnothing 13 mm), 3 × key L-wrenches (3, 4 and 5 AF).

Technical description

Application range external	6 - 70 mm
Application range internal	18 - 75 mm
Width	110 mm
Length	142 mm

Gauging force	2.6 N
Measurement technology	analogue
Type of product	2-point measuring device

Accessories

Spare contact point DM1 Disc anvil \varnothing 13 mm	428035 13
Spare contact point DM1 Disc anvil \varnothing 8 mm	428035 8