

 Mahr**Internal micrometer, Measuring range: 150-175mm****Order data**

Order number	427800 150-175
GTIN	2050001053664
Item class	43A

Description**Version:**

Lightweight, kink-proof tubular construction. Measuring spindle through hardened and ground. **Measuring faces hardened and spherical lapped.** Control elements and reading parts satin chrome-plated. From measuring range 100 - 125 mm with thermal insulation and locking lever.

Supplied with:

Micrometer in a sleeve.

Technical description

Barrel Ø	20 mm
Spindle Ø	8 mm
Measuring range	150 - 175 mm
Scale divisions	0.01 mm
Error limit	7 µm
Standard	DIN 863
Micrometer barrel graduations	1/50 mm
Measurement technology	analogue
Calibration	B10
Type of product	2-point internal micrometer

Services

DAkkS calibration Internal micrometer maximum
measuring range 200 mm

022450 200

Calibration Internal micrometer maximum measuring
range 200 mm

022440 200