



## XT internal micrometer set, Measuring range: 20-50mm



### Order data

Order number	428550 20-50
GTIN	5051102071370
Item class	46B

### Description

#### Version:

3-Point **XT inside micrometers**. Measuring spindle hardened and ground. Micrometer barrel with black scale, all reading parts satin chrome-plated. Ratchet for consistent measuring force. All gauges supplied with serial number and test certificate.

#### Application:

Blind holes and through holes, centring edges.

#### Supplied with:

Internal micrometers No. 428500 and setting rings with UKAS test certificate.

#### Optional extras:

Setting rings No. 484030, extension No. 428510.

#### Spare part:

Micrometer heads No. 428605.

### Technical description

Measuring range	20 - 50 mm
Number of setting rings	2
Number of micrometers	3
Setting ring $\varnothing$	20 / 35 mm

Standard	DIN 863
Micrometer barrel graduations	1/50 mm
Measurement technology	analogue
Packaging	sturdy box
Calibration	S6
Type of product	3-point internal micrometer

### Services

Calibration Internal micrometer set Measuring range 20-50 mm	020550 20-50
--	--------------

### Accessories

Setting ring DIN 2250 C Nominal size Ø 30 mm	484030 30
Setting ring DIN 2250 C Nominal size Ø 40 mm	484030 40
XT internal micrometer Measuring range 25-35 mm	428500 25-35
Setting ring DIN 2250 C Nominal size Ø 22 mm	484030 22
Extension for internal micrometers Type 4/150	428510 4/150
XT internal micrometer Measuring range 35-50 mm	428500 35-50
XT internal micrometer Measuring range 20-25 mm	428500 20-25
Replacement XT measuring head Measuring range 35-50 mm	428605 35-50
Measuring jaws set 3 pieces Measuring range 20-25 mm	428745 20-25
Return spring set 3 pieces Measuring range 20-25 mm	428746 20-25
Measuring jaws set 3 pieces Measuring range 25-35 mm	428745 25-35
Return spring set 3 pieces Measuring range 25-35 mm	428746 25-35
Measuring jaws set 3 pieces Measuring range 35-50 mm	428745 35-50
Return spring set 3 pieces Measuring range 35-50 mm	428746 35-50