



## XT internal micrometer, Measuring range: 200-225mm



### Order data

Order number	428500 200-225
GTIN	5051102001353
Item class	46B

### Description

#### Version:

3-Point **XT inside micrometers**. Measuring spindle hardened and ground. Micrometer barrel with black scale, all reading parts satin chrome-plated. Ratchet for consistent measuring force. All gauges supplied with serial number and test certificate. For blind hole measurements from size 12.5 – 16. Internal micrometers for maximum precision. Fixed carbide measuring jaws, from size 12.5 with carbide inserts.

#### Application:

Blind holes and through holes, centring edges.

#### Optional extras:

Setting rings No. 484030, extension No. 428510.

#### Spare part:

Micrometer heads No. 428605.

### Technical description

Standard measuring depth	115 mm
Measuring depth with extension	265 mm
Dimension a	0.5 mm

Measuring range	200 - 225 mm
Error limit	0.008 mm
Scale divisions	0.005 mm
Standard	DIN 863
Micrometer barrel graduations	1/50 mm
Measurement technology	analogue
Packaging	sturdy box
Calibration	B6
Type of product	3-point internal micrometer

## Services

Calibration 3-point internal micrometer maximum measuring range 300 mm	022500 300
--	------------

## Accessories

Extension for internal micrometers Type 5/150	428510 5/150
Setting ring DIN 2250 C Nominal size Ø 225 mm	484030 225
Setting ring DIN 2250 C Nominal size Ø 210 mm	484030 210