



XT internal micrometer set, Measuring range: 150-200mm



Order data

Order number	428550 150-200
GTIN	5051102040703
Item class	46B

Description

Version:

3-Point **XT inside micrometers**. Measuring spindle hardened and ground. Micrometer barrel with black scale, all reading parts satin chrome-plated. Ratchet for consistent measuring force. All gauges supplied with serial number and test certificate.

Application:

Blind holes and through holes, centring edges.

Supplied with:

Internal micrometers No. 428500 and setting rings with UKAS test certificate.

Optional extras:

Setting rings No. 484030, extension No. 428510.

Spare part:

Micrometer heads No. 428605.

Technical description

Number of setting rings	1
Setting ring \varnothing	175 mm
Measuring range	150 - 200 mm
Number of micrometers	2

Standard	DIN 863
Micrometer barrel graduations	1/50 mm
Measurement technology	analogue
Packaging	sturdy box
Calibration	S6
Type of product	3-point internal micrometer

Services

CalibrationInternal micrometer set Measuring range 150-200 mm	020550 150-200
---	----------------

Accessories

Setting ringDIN 2250 C Nominal size Ø 160 mm	484030 160
Replacement XT measuring head Measuring range 175-200 mm	428605 175-200
Setting ringDIN 2250 C Nominal size Ø 190 mm	484030 190
XT internal micrometer Measuring range 150-175 mm	428500 150-175
Replacement XT measuring head Measuring range 150-175 mm	428605 150-175
Extension for internal micrometers Type 5/150	428510 5/150
XT internal micrometer Measuring range 175-200 mm	428500 175-200
Measuring jaws set3 pieces Measuring range 150-175 mm	428745 150-175
Return spring set3 pieces Measuring range 150-175 mm	428746 150-175
Measuring jaws set3 pieces Measuring range 175-200 mm	428745 175-200
Return spring set3 pieces Measuring range 175-200 mm	428746 175-200