

Garant
Stainless straight edge in a case, Length: 100mm

Order data

Order number	460095 100
GTIN	4045197444271
Item class	41H

Description
Version:

Hardened, ground, and precision lapped straight edge. Wedge shaped cross section tapering to a point for inspection even in corners, grooves, cut outs etc. With plastic insulated handle to protection against body heat.

Made of **stainless steel**. **Both bevels anti-glare matt finished.**

Note:

The straightness tolerance of the measuring edge refers to a displacement range of $\pm 15^\circ$ to the symmetry plane.

Technical description

Straightness tolerance of the measuring edge	0.002 mm
Length	100 mm
Standard	DIN 874
Material	stainless steel
Surface chamfer	non-glare matt finish
Packaging	Wallet
Calibration	F6
Type of product	Straight edge

Services

DAkKS calibration	Straight edge maximum length 500 mm	026010 500
Calibration	Straight edge maximum length 200 mm	026000 200