



Vertical toggle clamp with horizontal base, Type: 4



Order data

Order number	376508 4
GTIN	4020772390310
Item class	32S

Description

Version:

With horizontal base for fixing to base plates etc.

Application:

For quick clamping and releasing of parts in series production or for installation as part of special clamping jigs. Suitable for clamping during drilling, reaming, grinding, bending, welding, fitting etc.

Technical description

Contact screw	M10×89 mm
overall length	143 mm
Hole spacing e	32 mm
Clamping force P2	3470 N
Clamping force P1	2500 N
Hole spacing f	45 mm

overall height	218 mm
Bore Ø d	8.3 mm
Type	376508 4
Clamping height H	43 mm
Type of product	Vertical toggle clamps