



Vertical toggle clamp with vertical base, Type: 1



Order data

Order number	376510 1
GTIN	4020772007805
Item class	35A

Description

Version:

With vertical base for fixing to ribs and for welded structures.

- **Compact design due to new handle.**
- **Ergonomic 2-component handle, very comfortable to use due to enlarged hand rest.**
- **Captive contact screw.**
- **Finger protection thanks to safety clamping mechanism no trap points.**

Application:

For quick clamping and releasing of parts in series production or for installation as part of special clamping jigs. Suitable for clamping during drilling, reaming, grinding, bending, welding, fitting etc.

Technical description

Clamping force P2	1100 N
overall length	61 mm
Bore \varnothing d	4.5 mm
overall height	109 mm

Hole spacing e	16 mm
Contact screw	M5×30 mm
Clamping force P1	600 N
Type	6802J
Clamping height H	23.5 - 25 mm
Type of product	Vertical toggle clamps