



## Vertical toggle clamp with vertical base, Type: 2



### Order data

Order number	376510 2
GTIN	4020772007812
Item class	35A

### Description

#### Version:

With vertical base for fixing to ribs and for welded structures.

- **Compact design due to new handle.**
- **Ergonomic 2-component handle, very comfortable to use due to enlarged hand rest.**
- **Captive contact screw.**
- **Finger protection thanks to safety clamping mechanism no trap points.**

#### Application:

**For quick clamping and releasing of parts in series production** or for installation as part of special clamping jigs. Suitable for clamping during drilling, reaming, grinding, bending, welding, fitting etc.

### Technical description

Bore $\varnothing$ d	5.5 mm
Contact screw	M6x35 mm
overall height	144.5 mm
Hole spacing e	20 mm

overall length	78 mm
Clamping force P2	1200 N
Clamping force P1	800 N
Type	6802J
Clamping height H	28.5 - 32 mm
Type of product	Vertical toggle clamps