



XT internal micrometer, Measuring range: 100-125mm



Order data

Order number	428500 100-125
GTIN	5051102001346
Item class	46B

Description

Version:

3-Point **XT inside micrometers**. Measuring spindle hardened and ground. Micrometer barrel with black scale, all reading parts satin chrome-plated. Ratchet for consistent measuring force. All gauges supplied with serial number and test certificate. For blind hole measurements from size 12.5 – 16. Internal micrometers for maximum precision. Fixed carbide measuring jaws, from size 12.5 with carbide inserts.

Application:

Blind holes and through holes, centring edges.

Optional extras:

Setting rings No. 484030, extension No. 428510.

Spare part:

Micrometer heads No. 428605.

Technical description

Measuring range	100 - 125 mm
Measuring depth with extension	265 mm
Dimension a	0.5 mm

Standard measuring depth	115 mm
Error limit	0.006 mm
Scale divisions	0.005 mm
Standard	DIN 863
Micrometer barrel graduations	1/50 mm
Measurement technology	analogue
Packaging	sturdy box
Calibration	B6
Type of product	3-point internal micrometer

Services

Calibration 3-point internal micrometer maximum measuring range 200 mm	022500 200
DAkkS calibration 3-point internal micrometer maximum measuring range 200 mm	022510 200

Accessories

Setting ring DIN 2250 C Nominal size \varnothing 110 mm	484030 110
Setting ring DIN 2250 C Nominal size \varnothing 100 mm	484030 100
Setting ring DIN 2250 C Nominal size \varnothing 125 mm	484030 125
Extension for internal micrometers Type 5/150	428510 5/150
Replacement XT measuring head Measuring range 100-125 mm	428605 100-125