



## XT internal micrometer, Measuring range: 8-10mm



### Order data

Order number	428500 8-10
GTIN	5051102212438
Item class	46B

### Description

#### Version:

3-Point **XT inside micrometers**. Measuring spindle hardened and ground. Micrometer barrel with black scale, all reading parts satin chrome-plated. Ratchet for consistent measuring force. All gauges supplied with serial number and test certificate. "Micro" - version with better resolution of 2 µm.

#### Application:

Blind holes and through holes, centring edges.

#### Optional extras:

Setting rings No. 484030, extension No. 428510.

#### Spare part:

Micrometer heads No. 428605.

### Technical description

Standard measuring depth	58 mm
Measuring range	8 - 10 mm
Measuring depth with extension	121 mm

Dimension a	1.9 mm
Error limit	0.004 mm
Scale divisions	0.002 mm
Standard	DIN 863
Micrometer barrel graduations	1/50 mm
Measurement technology	analogue
Packaging	sturdy box
Calibration	B6
Type of product	3-point internal micrometer

## Services

Calibration 3-point internal micrometer maximum measuring range 20 mm	022500 20
DAkkS calibration 3-point internal micrometer maximum measuring range 200 mm	022510 200

## Accessories

Setting ring DIN 2250 C Nominal size $\varnothing$ 8 mm	484030 8
Replacement XT measuring head Measuring range 8-10 mm	428605 8-10
Setting ring DIN 2250 C Nominal size $\varnothing$ 9 mm	484030 9
Setting ring DIN 2250 C Nominal size $\varnothing$ 10 mm	484030 10
Extension for internal micrometers Type 1/63	428510 1/63
Measuring jaws set 3 pieces Measuring range 8-10 mm	428745 8-10
Return spring set 3 pieces Measuring range 8-10 mm	428746 8-10