



Vertical toggle clamp with horizontal base, stainless, Type: 1



Order data

Order number	376505 1
GTIN	4020772008888
Item class	35A

Description

Version:

With horizontal base for fixing to base plates etc.

- **Compact design due to new handle.**
- **Ergonomic 2-component handle, very comfortable to use due to enlarged hand rest.**
- **Captive contact screw.**
- **Finger protection thanks to safety clamping mechanism no trap points.**

Application:

For quick clamping and releasing of parts in series production or for installation as part of special clamping jigs. Suitable for clamping during drilling, reaming, grinding, bending, welding, fitting etc.

Technical description

overall height	98 mm
Bore Ø d	4.5 mm
Hole spacing f	22.5-26 mm
overall length	61 mm

Contact screw	M5×30 mm
Hole spacing e	16 mm
Clamping force P2	1100 N
Clamping force P1	600 N
Type	6800NIJ
Clamping height H	19 mm
Type of product	Vertical toggle clamps