



## Vertical toggle clamp with vertical base, Type: 4



### Order data

Order number	376510 4
GTIN	4020772007843
Item class	35A

### Description

#### Version:

With vertical base for fixing to ribs and for welded structures.

- **Compact design due to new handle.**
- **Ergonomic 2-component handle, very comfortable to use due to enlarged hand rest.**
- **Captive contact screw.**
- **Finger protection thanks to safety clamping mechanism no trap points.**

#### Application:

**For quick clamping and releasing of parts in series production** or for installation as part of special clamping jigs. Suitable for clamping during drilling, reaming, grinding, bending, welding, fitting etc.

### Technical description

Clamping force P2	3000 N
overall length	141 mm
Clamping force P1	1700 N
overall height	244 mm

Contact screw	M8×65 mm
Hole spacing e	32 mm
Bore Ø d	8.6 mm
Type	6802J
Clamping height H	55.5 mm
Type of product	Vertical toggle clamps