



Vertical toggle clamp with angled base for side attachment, Type: 4



Order data

Order number	376520 4
GTIN	4020772007911
Item class	35A

Description

Version:

With angled base for side attachment.

- **Compact design due to new handle.**
- **Ergonomic 2-component handle, very comfortable to use due to enlarged hand rest.**
- **Captive contact screw.**
- **Finger protection thanks to safety clamping mechanism no trap points.**

Application:

For quick clamping and releasing of parts in series production or for installation as part of special clamping jigs. Suitable for clamping during drilling, reaming, grinding, bending, welding, fitting etc.

Technical description

Contact screw	M8×65 mm
Hole spacing f	32 mm
overall height	280 mm
Clamping force P2	3000 N

overall length	141 mm
Clamping force P1	2000 N
Bore \varnothing d	8.5 mm
Hole spacing e	32 mm
Type	6803J
Clamping height H	60 mm
Type of product	Vertical toggle clamps