



Vertical toggle clamp with vertical base, Type: 5



Order data

Order number	376510 5
GTIN	4020772007850
Item class	35A

Description

Version:

With vertical base for fixing to ribs and for welded structures.

- **Compact design due to new handle.**
- **Ergonomic 2-component handle, very comfortable to use due to enlarged hand rest.**
- **Captive contact screw.**
- **Finger protection thanks to safety clamping mechanism no trap points.**

Application:

For quick clamping and releasing of parts in series production or for installation as part of special clamping jigs. Suitable for clamping during drilling, reaming, grinding, bending, welding, fitting etc.

Technical description

Clamping force P2	5000 N
Clamping force P1	3000 N
Bore \varnothing d	8.5 mm
Hole spacing e	45 mm

overall height	301 mm
Contact screw	M12×80 mm
overall length	195 mm
Type	6802J
Clamping height H	66 mm
Type of product	Vertical toggle clamps