



## Horizontal toggle clamp with horizontal base, Type: 0



### Order data

|              |               |
|--------------|---------------|
| Order number | 376610 0      |
| GTIN         | 4020772008048 |
| Item class   | 35A           |

### Description

#### Version:

Captive contact screws.

Compact design due to new handle.

Ergonomic 2-component handle, very comfortable to use due to enlarged hand rest.

With horizontal base for fixing to base plates etc.

#### Application:

**For quick clamping and releasing of parts in series production** or for installation as part of special clamping jigs. Suitable for clamping during drilling, reaming, grinding, bending, welding, fitting etc.

### Technical description

|                   |              |
|-------------------|--------------|
| overall height    | 23 mm        |
| Hole spacing f    | 16 mm        |
| Hole spacing e    | 11.5-14.5 mm |
| Clamping force P1 | 250 N        |
| Contact screw     | M4x25 mm     |
| overall length    | 79 mm        |
| Clamping force P2 | 400 N        |

|                   |                         |
|-------------------|-------------------------|
| Bore Ø d          | 4.6 mm                  |
| Type              | 6830J                   |
| Clamping height H | 14.5 mm                 |
| Type of product   | Horizontal toggle clamp |