



Push-pull toggle clamp with angled base, Type: 1



Order data

Order number	376710 1
GTIN	4020772008406
Item class	35A

Description

Version:

With **compound action**. Opening prevented by self-locking mechanism.

- **Rivet made of stainless steel, bearings greased.**
- **With long push-pull guide.**
- **Handle can be moved to any angle.**
- **With hardened and galvanised contact screw.**
- **Detachable angled base, permitting fixing to sheet metal walls.**

Application:

For use in special clamping fixtures for drilling, reaming, grinding, bending, welding, fitting etc.

Optional extras:

Angled base No. 376730.

Note:

- **Size 0 and 3 also available in stainless steel!**

Technical description

Clamping height b to centre of screw	15 mm
Bore \varnothing d	4.5 mm
Clamping force P (pressure and traction)	1000 N

Angled base width K	30 mm
Contact screw	M4×20 mm
Hole spacing f	16 - 19.5 mm
Clamping range	20 mm
thread at front of clamp	M12×1,5 mm
Overall height H	60.5 mm
Overall length L	185 mm
Type	6841J
Type of product	Push-pull toggle clamp

Accessories

Angled base sturdy Type 2	376730 2
Angled base sturdy Type 5	376730 5
Angled base sturdy Type 3	376730 3