



Vertical toggle clamp with angled base for side attachment, Type: 1



Order data

Order number	376520 1
GTIN	4020772007881
Item class	35A

Description

Version:

With angled base for side attachment.

- **Compact design due to new handle.**
- **Ergonomic 2-component handle, very comfortable to use due to enlarged hand rest.**
- **Captive contact screw.**
- **Finger protection thanks to safety clamping mechanism no trap points.**

Application:

For quick clamping and releasing of parts in series production or for installation as part of special clamping jigs. Suitable for clamping during drilling, reaming, grinding, bending, welding, fitting etc.

Technical description

Contact screw	M5×30 mm
Clamping force P1	800 N
Clamping force P2	1100 N
overall height	125 mm

Hole spacing e	14 mm
Bore Ø d	4.5 mm
Hole spacing f	20 mm
overall length	61 mm
Type	6803J
Clamping height H	27 mm
Type of product	Vertical toggle clamps