

**Garant****Stainless straight edge in a case, Length: 150mm****Order data**

Order number	460095 150
GTIN	4045197444295
Item class	41H

**Description****Version:**

Hardened, ground, and precision lapped straight edge. Wedge shaped cross section tapering to a point for inspection even in corners, grooves, cut outs etc. With plastic insulated handle to protection against body heat.

Made of **stainless steel**. **Both bevels anti-glare matt finished.**

**Note:**

The straightness tolerance of the measuring edge refers to a displacement range of  $\pm 15^\circ$  to the symmetry plane.

**Technical description**

Length	150 mm
Straightness tolerance of the measuring edge	0.003 mm
Standard	DIN 874
Material	stainless steel
Surface chamfer	non-glare matt finish
Packaging	Wallet
Calibration	F6
Type of product	Straight edge

**Services**

DAkKS calibration	Straight edge maximum length 500 mm	026010 500
Calibration	Straight edge maximum length 200 mm	026000 200